

# Shaft Collar

## Shaft Collar



Set Screw - Standard / Wide Type  
267



Compact  
268



Clamp, Standard Type  
269



Compact  
270



Split, Standard Type  
271



Compact  
272



Balanced Type  
272



Standard with Urethane, Clamp Type  
273



Split  
273



Compact with Urethane, Clamp Type  
273



Split  
273



With Threaded Inserts (Lightweight) - Plastic Type  
274



Aluminum Type  
274



For Bearing Mounting - Set Screw Type  
275



Compact, Set Screw  
276



For Bearing Mounting - Clamp Type  
277



Clamp, Compact Type  
278



Set Screw - 2-Hole / 2-Tapped Type  
279



4-Hole / 4-Tapped Type  
279



Clamp - 2-Hole Counterbored / 3-Hole Counterbored Type  
280



2-Hole / 2-Tapped Type  
281



3-Hole / 3-Tapped Type  
282



Split - 2 Hole / 2-Tapped Type  
283



Wedge - 2-Hole / 2-Tapped Type  
285



3 Hole / 3-Tapped Type  
285



Compact Wedge with Clamp Lever, D Cut Type  
286



Wedge, Side Mount Hole Type  
286



Standard with Clamp Lever, Clamp  
287



D Cut Type  
287



Side Mount Hole Type  
287



Compact with Clamp Lever, D Cut Type  
288



Side Mount Hole Type  
288



D Cut Standard - Set Screw  
289



Clamp Type  
289



Split  
289



D Cut Compact - Clamp  
290



Split  
290



Standard, Side Mount Hole, Clamp Type  
291



Split  
291



Compact, Side Mount Hole, Clamp Type  
292



Split  
292



2 Flats, Clamp Standard Type  
293



Clamp, Cut Surface Mount Hole Type  
293



2 Flats, Clamp, Side Mount Hole Type  
293



Split, Cut Surface Mount Hole Type  
293



Hinged  
294



One-Touch Standard / One-Touch Mount Hole Type  
294



Threaded Bore - Set Screw Type  
295



Clamp Type  
295



Key Relief Groove, Set Screw Type  
296



Clamp Type  
296