# What are C-VALUE Products?



## Variations

Lineup of all 6 types in different shapes and materials. For light load, intermediate and low speed, and medium rotational accuracy applications, we offer the stainless steel and flanged type rarely available from other manufacturers! You can select the most suitable type according to your needs.

Small Ball Bearing C-B6 ZZ		Max. Cost Reduction Rate	Stainless Steel Small Ball Bearing C-SB6 ZZ		Max. Cost Reduction Ra
	Available I.D.	51% OFF		Available I.D.	
	2~8mm		$\bigcirc$	2~8mm	55% OFF
	Page			Page	
	P.990			P.994	
Deep Groove Ball Bearing C-B6		Max. Cost Reduction Rate	Stainless Steel Deep Groove Ball Bearing C-SB6		Max. Cost Reduction R
	Available I.D.			Available I.D.	
	10~40mm	60%		10~30mm	61%
	Page	OFF		Page	OFF
	P.992			P.996	
Deep Groove Ball Bearing with Flange C-FL6		Max. Cost Reduction Rate	Stainless Steel Deep Groove Ball Bearing with Flange C-SFL6		Max. Cost Reduction R
	Available I.D.	60% OFF		Available I.D.	
	3~25mm			3~15mm	58%
	Page			Page	OFF
	P.998	1		P.1000	1

## Specifications & Standards

Cautions on Selection

Two differences between C-VALUE Products and the MISUMI Similar Products are:

#### ① Allowable Load

**2** Bearing Internal Clearance

When you select a product, verify the check points  $\bigcirc$  and  $\oslash$  in the product page specification table (values in the red frame) and use the product accordingly. 'See the telow table to the exemple of specification comparison.

#### Specification Difference between MISUMI Similar Products and C-VALUE Products [Difference between B6901ZZ (MISUMI Similar Product) and C-B69001ZZ (C-VALUE Product)]

JIS B 1514 Class 0

outer rings, 💵 P.2243

\* MISUMI C-VALUE Products meet the above standards.

manufacturing process, so there will be no problem with the performance.

A minor blemish or dent may be found on the shielding area in rare occasions.

but our products have passed all the performance inspections in the

For details on the tolerance and allowable values of inner and

	MISUMI Similar Products	MISUMI C-VALUE Products		
Allowable Load	Basic Dynamic Load Rating (Cr): 2.89kN Basic Static Load Rating (Cor): 1.46kN	Basic Dynamic Load Rating (Cr): 2kN Basic Static Load Rating (Cor): 1kN		
Life	Basic Rated Life (With 2.89kN load)	Basic Rated Life (With 2kN load)    400,000 rotations		
	EX: Case Example (Rotating at Speed: 750 rpm, Load: 0.5kN) • 4,000 hours	EX: Case Example (Rotating at Speed: 750 rpm, Load: 0.5kN) 1,600 hours		
Bearing Internal Clearance	Min.:3µm Max.:18µm	Min.:6µm Max.:23µm		