

Nozzles

Nozzles



Product Name	Flat Air Nozzles - Standard	Wide Type	Compact	Air-Amplified Type	Air-Amplify Wide Type	Air-Amplify Compact Type
Page	1455	1456	1456	1457	1458	1458



90° Air Nozzles - Standard	Compact	Wide Type	Vertical Blow Type	High Flow Rate Blower Nozzles	Flat Air Nozzles for Blowers
1459	1459	1460	1460	1461	1462



High Pressure Blowers	Air Nozzles - Economy Type	Air Nozzles - De Laval Type	Spray Nozzles - Circular Spray Pattern - Standard	Air-Amplified Type	Nozzles with Swaged Sleeve Couplings	Point Nozzles
1462	1463	1463	1464	1464	1465	1465



Point Nozzles - Compact	Reverse Flow Prevention	Rotary Nozzles	Flow Rate Control Nozzles	Conical Spray Air Nozzles	Radial Air Nozzles	Air Blow Nozzles
1466	1466	1467	1467	1468	1468	1469, 1470



Pipe Nozzles	Copper Pipes for Air Blow / Nozzles with Attachment Plate	Steel Pipe Nozzles	Slit Steel Pipe Nozzles	Nozzles for Pipe Washing	Steel Hollows for Air Nozzles	Terminals for Nozzles
1471	1471	1472	1473	1473	1474	1474



Nozzle Joint	Spray Nozzles	Adjustable Hoses / Set	Adjustable Hoses Components / Installation Tools
1475	1476, 1477	1479	1480

Nozzles - Overview

■ Features

By installing to the pipe tip, efficient air / fluid blow can be achieved.
Various mount types and spray width are available for each product.

■ Applications

Air Nozzles: Dry, Dust Removal, Blow Off, Conveyance Support, Peeling, Drying, Cooling, Workpiece Protection, Smoke Emission, etc.

Spray Nozzles: Washing, Cooling, Dust Removal, Defrosting, etc.

Spray Pattern	Features		Air Nozzles					
Flat	For Air Compressor	Standard / ABS Plastic		Flat Air Nozzles Standard		Flat Air Nozzles Compact		Flat Air Nozzles Wide Type
		Standard / Metal		Flat Air Nozzles Standard		Flat Air Nozzles Compact		
		Space Saving / ABS Plastic		90° Air Nozzle Standard		90° Air Nozzle Compact		90° Air Nozzle Wide Type
		Space Saving / Metal		90° Air Nozzle Compact				
		Reduced Plumbing Man-hours / ABS Plastic		Flat Air Nozzles Tapped		90° Air Nozzle Vertical Blow Type		
		Energy Saving / PPS Resin		Air-Amplify Nozzles Standard * Aluminum machined products are available.		Air-Amplify Nozzles Compact		Air-Amplify Nozzles Wide Type
		Others		Air Nozzles - Economy Type Wide Blow Port		Air Nozzles - Economy Type Narrow Blow Port		Steel Pipe Nozzles Long Type
	For Air Blower	Standard / Metal		Blower Nozzles -SUS-		Blower Nozzles Aluminum		
Spot	For Air Compressor	Pipe Juncture / Metal		Air Blow Nozzles Small Dia. Stainless Steel Pipes		Air Blow Nozzles Copper Pipes for Air Blow		Air Blow Nozzles Pipe Nozzles
		Variable Type / Metal		Point Nozzles Angle Variable		Point Nozzles Swaged Sleeve Type		Point Nozzles Flow Rate Control
Circular		Circular / Plastic, Metal		Spray Nozzles - Circular Spray Pattern Standard		Spray Nozzles - Circular Spray Pattern Amplify Type		Air Nozzles - De Laval Type Metal Type
Diffusive		Diffusive / Metal		Conical Spray Nozzles		Radial Air Nozzles		Rotary Nozzles

Spray Pattern	Features		Spray Nozzles					
Fan-shaped	Wide-range Spray / Metal			Spray Nozzles Fan-shaped		Spray Nozzles Fan-shaped		
Circular, Spot	Point Spray / Metal			Spray Nozzles Straight Stream		Spray Nozzles Annular Shape		Spray Nozzles Full-Circular Shape
Multi-function	Spray Angle Adjustable, Mist Spray / Metal			Spray Nozzles Spray Angle Adjustable		Nozzles for Pipe Washing		Two-Fluid Nozzles

Others		Nozzle Joint / Metal		Nozzle Joint / PP Resin		Terminals for Nozzles / Metal		Adjustable Hoses / Plastic
								