

Factory Frame / Pipe Frame Standard Units - Overview

Standard Units Overview (P.891~P.906)

- With these pipe frame units, the part number and the number of the components are determined just by specifying the component types and each dimension.
- All the materials needed to construct a unit can be specified just a single Type Number.

Components List


[PFUB]

Number	Part Number	Name	Qty.	Listed Page
①	PFS28-Color-(T-133)	Pipe Frame	2	P.891
②	PFS28-Color-(D-103)	Pipe Frame	7	
③	PFS28-Color-(W-103)	Pipe Frame	8	
④	PFS28-Color-(H-133)	Pipe Frame	2	P.894
⑤	PBSN1	Metal Joint	14	
⑥	PBSN2	Metal Joint	8	
⑦	JBS005	Caster Attachment Parts	8	P.904
⑧	JBS006	Caster Attachment Parts	8	
⑨	PJ503-W (White)	Inner Cap	4	P.897
⑩	PHCHK100	Caster	2	P.903
⑪	PHCHS100	Caster with Stopper	2	

[FFUB]

Number	Part Number	Name	Qty.	Listed Page
①	FFA28-(T-133)	Factory Frame	2	P.880
②	FFA28-(D-110)	Factory Frame	7	
③	FFA28-(W-110)	Factory Frame	8	
④	FFA28-(H-133)	Factory Frame	2	P.881
⑤	FFB1	Metal Joint	14	
⑥	FFB2	Metal Joint	8	
⑦	JBS005	Caster Attachment Parts	8	P.904
⑧	JBS006	Caster Attachment Parts	8	
⑨	FFS103	Inner Cap	4	P.883
⑩	PHCHK100	Caster	2	P.903
⑪	PHCHS100	Caster with Stopper	2	

Assembly Drawing



For Shelf Panels

This unit doesn't include top panels or shelf panels. Please order separately.

For Top Shelf Panels

Select the product among the lineup from P.935~P.940.

M Material	Part Number	Listed Page
Double-Sided Melamine Resin Glued Laminated Plywood	MPBHA10, MPBHA15, MPBHA20	P.935
Laminated Plywood	PBHA12, PBHA16, PBHA20	
Single-Sided Rubber Glued Laminated Plywood (Standard)	NTBHA10, NTBHA14, NTBHA20	P.937
Single-Sided Rubber Glued Laminated Plywood (Antistatic)	ATBHA10, ATBHA14, ATBHA20	
Double-Sided Melamine Resin Glued Laminated Plywood with Soft Edge	MPBHAR10, MPBHAR15, MPBHAR20	P.939
Single-Sided Rubber Glued Laminated Plywood with Soft Edge (Standard)	NTBHAR10, NTBHAR14, NTBHAR20	
Single-Sided Rubber Glued Laminated Plywood with Soft Edge (Antistatic)	ATBHAR10, ATBHAR14, ATBHAR20	
Aluminum Glued Laminated Plywood with Soft Edge	ALBHAR10, ALBHAR15, ALBHAR20	

Ordering Example

Part Number - **A** - **B** - Color - **R** - **E** - **S**
select from the above table. W Dimension D Dimension Color - 10 - 32 - 32

For Shelf Panel mounting, use PJ706B (P.898) or FEB6 (P.881)

For Bottom Shelf Panels

Select the product among the lineup from P.935~P.940.

M Material	Part Number	Listed Page
Double-Sided Melamine Resin Glued Laminated Plywood	MPBH10, MPBH15, MPBH20	P.935
Laminated Plywood	PBH12, PBH16, PBH20	
Single-Sided Rubber Glued Laminated Plywood (Standard)	NTBH10, NTBH14, NTBH20	P.937
Single-Sided Rubber Glued Laminated Plywood (Antistatic)	ATBH10, ATBH14, ATBH20	
Double-Sided Melamine Resin Glued Laminated Plywood with Soft Edge	MPBHR10, MPBHR15, MPBHR20	P.939
Single-Sided Rubber Glued Laminated Plywood with Soft Edge (Standard)	NTBHR10, NTBHR14, NTBHR20	
Single-Sided Rubber Glued Laminated Plywood with Soft Edge (Antistatic)	ATBHR10, ATBHR14, ATBHR20	
Aluminum Glued Laminated Plywood with Soft Edge	ALBHR10, ALBHR15, ALBHR20	

Ordering Example

Part Number - **A** - **B** - Color - **E** - **S** - **X** - **Y**
select from the above table. W Dimension D Dimension Color - 32 - 32 - 32 - 32

For Shelf Panel mounting, use PJ706B (P.898) or FEB6 (P.881)