

Oil Free Bushings

Oil Free Bushings

Copper Alloy (Metal Type)



Product	Existing Products - Copper Alloy, Straight	C-VALUE Products - Copper Alloy, Straight	Existing Products - Copper Alloy, Flanged	C-VALUE Products - Copper Alloy, Flanged
Name Page	381/385/386	382	383/387	384

Copper Alloy (Metal Type)



Copper Alloy, Thrust	Flange Integrated Oil Free Bushings - Copper Alloy, Standard Flanged	Pilot Flanged	Center Flanged
388	389	390	390

Copper Alloy (Metal Type)

Bronze Casting (Metal Type)



Oil Free Copper Alloy Washers	Oil Free Bushings - Bronze, Straight	Bronze, Flanged	Bronze, Standard Flanged
390	391	391	392

Copper Alloy (Metal Type)



Oil Free Bushing Housing Units - Standard Flanged	With Dust Seals	Oil Free Bushing Housing Units - Pilot Flanged - Standard	Oil Free Bushing Housing Units - Center Flanged
393	393	394	392

Copper Alloy (Metal Type)



Tall / Wide Type	Tall Compact / Wide Compact Type
395	396

Casting (Metal Type)



Oil Free Bushings - Casting, Straight / Flanged	Oil Free Bushings - Cast Housing Units	Flange Integrated Oil Free Bushings - Casting
397	397	397

Multi-Layer LF



Oil Free Bushings - Multi-Layer LF Bushings	Oil Free Thrust Washers	Oil Free Bushings - High Precision
398	398	399

Multi-Layer LF



Oil Free Bushing Housing Units - Built-In Multi-Layer LF Bushings

399

Oil Free Bushing Block Style Housing Units - Built-In Multi-Layer LF Bushings

400

Resin (Resin Type)



Oil Free Bushings - Polyacetal Resin Type

401

PTFE Resin Type

401

Oil Free Resin Washers

402

Oil Free Bushing Flange Style Housing Units - Built-In Resin Bushings

402

Oil Free Bushing Block Style Housing Units - Built-In Resin Bushings

402

Material Features

Usage

Page

Copper Alloy (Metal Type)

- High shock resistance and high rigidity
- High corrosion resistance
- High temperature resistant

- Use in heavy load and low speed conditions
- Use in areas with parts requiring high accuracy
- Use for transporting heavy loads

P.381~
390

Bronze Casting (Metal Type)

- Minute motion is possible
- Excels in baking resistance

- Use in low load and high speed conditions
- Use in areas with small movements

P.391~
392

Casting (Metal Type)

- Absorb vibration

- Use in medium load and low speed conditions
- Use in areas to absorb vibration
- Use in areas where it is difficult to choose flamboyant colors, such as in the automotive industry

P.397

Multi-Layer LF (Multi-layer Type)

- Thin wall and compact
- High temperature resistant

- Use in heavy load and low speed conditions
- Use in limited space
- Low cost and frequently used in areas without requiring high precision

P.398

Resin (Resin Type)

- Conforms to Food Sanitation Law
- Excels in chemical resistance (*)

(*) PTFE type only

- Use in low load and high speed conditions
- Use in the insulating state
- Use in areas requiring strict hygiene control, such as in the food industry

P.401~
402