

V-Shaped Locating Block Sets

Flat Bottom Type

Features: The V Groove 70° Type has wider contacting surface compared to that of the 90° Type, suitable for misalignment prone rotating fixtures.

RoHS 10



Material: EN 1.1191 Equiv.
Hardness: 42-45HRC

25 / (1.5 6)


Type	Standard CVTA, CVTA12C CVTA16C, CVTAS CVTACS	Tapped Hole CVTAT CVTAST	Upper Plate Holding CVTAB CVTABS	V Groove 70° CVTAK	Long CVTAL
Mounting Dimension					
Upper Part					
Lower Part					

	Part Number Type	T	L	L1	L2	A	H	d	R	M (Coarse)	Unit Price 1 - 19 set(s)	Volume Discount Rate 20 ~
Standard	CVTA	-	35	22	23	25	14	9	4	-		
	CVTA12C	-	20	12	13	12	8	4.5	2	-		
	CVTA16C	-	25	-	16	16	-	-	2	-		
	CVTAS	-	25	16	19	25	11	7	4	-		
	CVTACS	-	25	17	20	-	-	-	2	-		
Tapped Hole Type	CVTAT	-	35	22	23	-	14	9	4	M8		
	CVTAST	-	25	16	19	25	11	7	4	M6		
Upper Plate Holding Type	CVTAB	12	35	20	26	20	9.5	5.5	2	-		
	16	-	-	22	28	25	14	9	4	-		
	19	-	-	-	-	-	-	-	-	-		
	CVTABS	12	25	14	22	20	9.5	5.5	2	-		
	16	-	-	16	24	25	11	7	4	-		
V Groove 70° Type	CVTAK	-	35	25	25	25	14	9	2	-		
	Long Type CVTAL	-	35	22	23	25	14	9	4	-		




Example

CVTA12C is a compact locating block which has the same width as that of the plate.



CVTA



CVTA12C



Ordering
Example

Part Number
CVTA
CVTAB12

V-Shaped Locating Block Sets


Plate Holding Type

■ **Features:** Plate holders on upper/lower sides enable easy mounting on thin flat bars.

RoHS 10


Material: EN 1.1191 Equiv.

Hardness: 42~45HRC



Type	Standard CVTB CVTBS	Tapped Hole CVTBST	Long CVTBL
Mounting Dimension			
Upper Part			
Lower Part			

	Part Number Type	T	L	L1	L2	A	H	d	R	M (Coarse)	Unit Price 1 ~ 19 set(s)	Volume Discount Rate 20~
Standard	CVTB	12	35	25	26	20	9.5	5.5	2	-		
		16		27	28	25	14	9	4			
		19										
	CVTBS	12	25	19	22	20	9.5	5.5	2			
		16		21	24	25	11	7	4			
		19										
Tapped Hole Type	CVTBST	16	25	21	24	25	11	7	4	M6		
Long Type	CVTBL	12	35	25	26	20	9.5	5.5	2	-		
		16										
		19		27	28	25	14	9	4			



Ordering
Example

Part Number
CVTB16