



Linear Guide Product List

■ Miniature Linear Guides

Specifications			Short	Standard	Long	Extra Long
Type	Rail	Block				
Existing Products	Standard Rail 	Standard	 P545~P548	 P533, P537	 P539, P543	 P553
		Wide	-	 P549	 P551	-
C-VALUE Products	Standard Rail 	Standard	-	 P535	 P541	-
Existing Products		Standard	-	 P555, P559	 P561, P564	-
		Wide	-	 P565	 P567	-
C-VALUE Products		Standard	-	 P557	-	-
Special Configurations			Dust Resistant	Heat Resistant	LTBC Plating	
			 P601	 P599	 P532	

Linear Guides for Medium/Heavy Load

Lubrication Units **MX** : Products applicable to Self-Lubrication Type

Specifications		Medium Load	Heavy Load	Super Heavy Load	Extra Super Heavy Load
Existing Products	Standard	MX  Carbon Steel: P569 Stainless Steel: P589	MX  Carbon Steel: P575 Stainless Steel: P589	-	-
	Standard with Dowel Holes	MX  P597	MX  P597	-	-
C-VALUE Products	Standard C-VALUE	 P571	 P577	 P583	 P587
Existing Products	With Plastic Retainers	 Carbon Steel: P573 Stainless Steel: P591	 Carbon Steel: P579 Stainless Steel: P593	 Carbon Steel: P581 Stainless Steel: P595	 P585
Special Configurations	Self-Lubrication			Dust Resistant	
	MX  P.569, P.575, P.589 P.597, P.603~P.606			Double-Sealed MX  P.603~P.606	With Metal Scrapers MX  P.603~P.606

